

Han HPR SP2-CM-for SCL-with lanyard




Image is for illustration purposes only. Please refer to product description.

Part number	09 40 021 5414
Specification	Han HPR SP2-CM-for SCL-with lanyard
HARTING eCatalogue	https://harting.com/09400215414

Identification

Category	Accessories
Series of hoods/housings	Han® HPR
Type of accessory	Protection cover
Description of the accessory	for hoods With fixing cord (loop)

Version

Size	SP2
Locking type	Screw locking
Details	Please note that when using the metal protection cover the connectors only can be used without voltage applied or a reduced voltage of max. 2000V. Please note that the use of the protection cover is needed to protect the Han® HC 650 / HC 800 when dropped acc. IEC 61984.

Technical characteristics

Tightening torque (screw locking)	6 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	96 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140400023
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467