

VarioShell® HC350/250 insulation cover



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 124 9911
Specification	VarioShell® HC350/250 insulation cover
HARTING eCatalogue	https://harting.com/09401249911

Identification

Category	Accessories
Series	Han® HC Modular
Identification	350
Series of hoods/housings	Han® HPR VarioShell
Type of accessory	Protection cover
Description of the accessory	for cable shoes

Technical characteristics

Rated voltage	2,500 V
Rated impulse voltage	12 kV
Pollution degree	3
Overvoltage category	II
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C

Material properties

Material (hood/housing)	Polycarbonate (PC)
-------------------------	--------------------

Commercial data

Packaging size	1
Net weight	33.91 g
Country of origin	China
European customs tariff number	85389099



Pushing Performance
Since 1945

Commercial data

GTIN	5713140279483
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467