

## Han 10HPR-Compact-HBM-DL



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR Compact
Type of hood/housing	Bulkhead mounted housing
Type	Low construction

### Version

Size	10 B
Locking type	Double locking lever
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Tightening torque	3 Nm Fixing screws M6
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP6K9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated

## Material properties

Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	205 g
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466