

RJI RJ45 GL Comp. plug Cat6A 8p 1=100pcs



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1524
Specification	RJI RJ45 GL Comp. plug Cat6A 8p 1=100pcs
HARTING eCatalogue	https://harting.com/09451511524

Identification

Category	Connectors
Series	HARTING RJ Industrial® RJ45
Element	Cable connector
Specification	Compact version

Version

Termination method	Piercing termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Pack contents	Packaging with 100 sets

Technical characteristics

Conductor cross-section	0.08 ... 0.22 mm ² Stranded
Conductor cross-section [AWG]	AWG 28 ... AWG 24 Stranded
Wire outer diameter	1.05 mm
Rated current	1.5 A
Rated voltage	150 V AC
Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s

Technical characteristics

Insulation resistance	>1000 MΩ
Contact resistance	≤20 mΩ
Limiting temperature	-40 ... +70 °C
Relative humidity	95 % Non-condensing (operation)
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20
Cable diameter	5 ... 6.5 mm
Test voltage U _{DC}	1 kV (contact-contact) 1 kV (contact-ground)

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	480 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140224377
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408