

## Han3M RJ45 Cat5 coupler 8p



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Connectors
Series	RJ45
Series of hoods/housings	Han A®
Element	Double coupling
Specification	incl. installation frame metal

### Version

Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
	10 Mbit/s
Data rate	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	IP67

### Material properties

Material (hood/housing)	Zinc die-cast
-------------------------	---------------

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	127 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059634
eCl@ss	27440190 Industry connector (unspecified)
ETIM	EC001264
UNSPSC 24.0	39121409