

## Han3A RJ45 Cat5 coupler 8p plastic



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 225 1107
Specification	Han3A RJ45 Cat5 coupler 8p plastic
HARTING eCatalogue	<a href="https://harting.com/09452251107">https://harting.com/09452251107</a>

### Identification

Category	Connectors
Series	RJ45
Series of hoods/housings	Han A <sup>®</sup>
Element	Double coupling
Specification	incl. installation frame metal

### Version

Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Polycarbonate (PC)
-------------------------	--------------------



Pushing Performance  
Since 1945

## Material properties

Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	27.667 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059788
eCl@ss	27440190 Industry connector (unspecified)
ETIM	EC001264
UNSPSC 24.0	39121409