

Han3A RJ45 Cat5 PFT 8p angled plastic



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 225 1108
Specification	Han3A RJ45 Cat5 PFT 8p angled plastic
HARTING eCatalogue	https://harting.com/09452251108

Identification

Category	Connectors
Series	RJ45
Series of hoods/housings	Han A [®]
Element	Panel feed through
Specification	Angled

Version

Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Fixing	Screwable in cover plates

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	IP67



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	35 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059795
eCl@ss	27440113 Rectangular connectors (set)
ETIM	EC002636
UNSPSC 24.0	39121408