

PP-V4-CA-USB2A-PP/PP-P-P-STR-3.0



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 445 1904
Specification	PP-V4-CA-USB2A-PP/PP-P-P-STR-3.0
HARTING eCatalogue	https://harting.com/09454451904

Identification

Category	System cabling
Series	HARTING PushPull (V4)
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING PushPull (V4) USB 2.0 Type A
Connector 2	HARTING PushPull (V4) USB 2.0 Type A
Type of cable	Copper cable (round)

Version

Cable length	3 m
Number of cores	4
Core structure	2x AWG 26/7 2x AWG 24/11
Shielding	Shielded

Technical characteristics

Rated current	1.5 A
Rated voltage	30 V DC
Data rate	480 Mbit/s
Insulation resistance	$> 1.6 \times 10^6 \Omega$
Contact resistance	$\leq 30 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C



Pushing Performance
Since 1945

Technical characteristics

Insertion force	≤35 N
Withdrawal force	≥15 N
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	4.9 mm
Test voltage $U_{r.m.s.}$	0.5 kV (contact-contact) 0.5 kV (contact-ground)
Impedance	90 Ω ±15 %

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Sn over Ni Termination side Au over Ni Mating side
Material (cable)	PVC
Colour (cable)	Black
Material (overmoulding)	Polyamide (PA)
Colour (overmoulding)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

Commercial data

Packaging size	1
Net weight	159 g
Country of origin	Malaysia
European customs tariff number	85444290



Pushing Performance
Since 1945

Commercial data

GTIN	5713140258143
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600