

## har-port USB 3.0 A-A PFT white



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1919
Specification	har-port USB 3.0 A-A PFT white
HARTING eCatalogue	<a href="https://harting.com/09454521919">https://harting.com/09454521919</a>

### Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 3.0

### Version

Connection type	Type A jack - type A jack
Fixing	Screwable in cover plates

### Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

### Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	White
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Material properties

California Proposition 65 substances	Not contained
--------------------------------------	---------------

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	16.4 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140222939
eCl@ss	27060304 Appliance cord (data cable)
ETIM	EC002599
UNSPSC 24.0	43202222