

har-stop



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 2500
Specification	har-stop
HARTING eCatalogue	https://harting.com/09454532500

Identification

Category	Operator interfaces
Series	har-stop
Element	Emergency stop buttons
Specification	foolproof

Version

Diameter of the mounting hole	30.5 mm
Details	This item requires additional contact blocks and a module holder to be functional. Please select these under "Matching Products".

Technical characteristics

Actuation path	6 mm
Tightening torque	≤2.5 Nm Fixing nut
Operating temperature	-30 ... +70 °C
Storage temperature	-50 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67
Thickness of the panel	1.5 ... 8 mm

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	EN 60947-5-1 EN 60947-5-5 EN ISO 13850
UL / CSA	UL 60947-5-1 NISD2.E534797 CSA C22.2 No. 60947-1:22 NISD8.E534797

Commercial data

Packaging size	10
Net weight	32 g
Country of origin	Germany
European customs tariff number	85365080
GTIN	5713140450172
eCl@ss	27371212 Front element for mushroom push-button actuators
ETIM	EC001038
UNSPSC 24.0	39122221