

Calotte green



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 2608
Specification	Calotte green
HARTING eCatalogue	https://harting.com/09454532608

Identification

Category	Operator interfaces
Series	har-light
Type of accessory	Calotte

Version

Diameter of the mounting hole	30.5 mm
-------------------------------	---------

Material properties

Colour (accessories)	Green
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 60947-5-1 NKCR.E534795 CSA C22.2 No. 60947-5-1:22 NKCR7.E534795
----------	---



Pushing Performance
Since 1945

Commercial data

Packaging size	10
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140449992
eCl@ss	27371231 Dome, refractor
ETIM	EC001072
UNSPSC 24.0	39111815