

## Han3A RJ45 PFT HIFF adapter



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Connectors
Series	RJ45
Series of hoods/housings	Han A®
Element	Adapter
Specification	To mount HIFF inserts

### Version

Size	3 A
Shielding	Unshielded

### Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	3 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140060944
eCl@ss	27440210 Fixing element for industrial connectors
ETIM	EC002310
UNSPSC 24.0	39121466