

Han3A RJ45 Hybrid PFT housing EMC



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 515 0028
Specification	Han3A RJ45 Hybrid PFT housing EMC
HARTING eCatalogue	https://harting.com/09455150028

Identification

Category	Accessories
Series of hoods/housings	Han [®] 3 A RJ45 Hybrid
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	incl. flat seal and thermoplastic adapter for direct device integration

Material properties

Material (hood/housing)	metal, EMC
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Commercial data

Packaging size	1
Net weight	35.6 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140060951



Pushing Performance
Since 1945

Commercial data

eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466