

## Han3A RJ45 Hybrid power jack SMD



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 525 0040
Specification	Han3A RJ45 Hybrid power jack SMD
HARTING eCatalogue	<a href="https://harting.com/09455250040">https://harting.com/09455250040</a>

### Identification

Category	Connectors
Series	RJ45
Identification	Hybrid
Series of hoods/housings	Han A®
Element	Power module
Specification	for direct device integration

### Version

Termination method	Reflow soldering termination (SMT)
Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	0

### Technical characteristics

Conductor cross-section	1.5 mm <sup>2</sup>
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

## Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	100
Net weight	4.2 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140060982
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522