

Han3A RJ45 Hybrid power jack SMD T&R



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|--------------------------|-------------------------------|
| Category | Connectors |
| Series | RJ45 |
| Identification | Hybrid |
| Series of hoods/housings | Han A® |
| Element | Power module |
| Specification | for direct device integration |

Version

| | |
|--------------------|--|
| Termination method | Reflow soldering termination (SMT) |
| Size | 3 A |
| Shielding | Fully shielded, 360° shielding contact |
| Number of contacts | 0 |
| Pack contents | 100 pieces on reel |

Technical characteristics

| | |
|-------------------------|----------------|
| Conductor cross-section | 1.5 mm² |
| Limiting temperature | -40 ... +70 °C |
| Mating cycles | ≥500 |

Material properties

| | |
|------------|-----------|
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |

Material properties

| | |
|--------------------------------------|-----------------------|
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel Naphthalene |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
| PROFINET | Yes |

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 100 |
| Net weight | 7.1 g |
| Country of origin | Romania |
| European customs tariff number | 85366990 |
| GTIN | 5713140060999 |
| eCl@ss | 27440205 Contact insert for industrial connectors |
| ETIM | EC000438 |
| UNSPSC 24.0 | 39121522 |