

USB 2.0 HIFF Bulkhead coupler type A-A



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 545 1901
Specification	USB 2.0 HIFF Bulkhead coupler type A-A
HARTING eCatalogue	https://harting.com/09455451901

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	USB
Element	Coupler
Specification	USB 2.0 type A
Adapter for	HIFF version

Version

Shielding	Fully shielded, 360° shielding contact
Number of contacts	4

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

Material properties

California Proposition 65 substances	Lead Nickel
--------------------------------------	----------------

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	8 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140061439
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408