

## HAR PROFINET Typ A 4xAWG22/1 PVC 50m




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 600 0140
Specification	HAR PROFINET Typ A 4xAWG22/1 PVC 50m
HARTING eCatalogue	<a href="https://harting.com/09456000140">https://harting.com/09456000140</a>

### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)
Description of the cable	Flame retardant Largely oil resistant Sunlight resistant
Printing on cable	HARTING INDUSTRIAL ETHERNET STANDARD CABLE CAT 5 PLUS * 22AWG (SHIELDED) (UL) E333432 VERIFIED CAT 5E CMG 75°C or PLTC or AWM 21694 600V FT4 SUN RES * 094560001000100 "Metermarkierung" "Jahr/Auftragsnummer""HARTING-LOGO"
Features	Suitable for permanent installation

### Version

Cable length	50 m
Number of cores	4
Core structure	4x AWG 22/1

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +75 °C unmoved -20 ... +60 °C moved
Cable diameter	6.3 ... 6.7 mm



Pushing Performance  
 Since 1945

## Technical characteristics

Minimum bending radius	7.5x Cable diameter (repeated bending) 3x Cable diameter (singular bending)
Tensile strength	≤150 N
Test voltage $U_{r.m.s.}$	2 kV Wire / wire / shielding
Coupling attenuation @ 20 °C / 10 MHz	10 mΩ/m
Conductor resistance @ 20 °C	≤115 Ω/km
Insulation resistance @ 20 °C	≥500 MΩ x km
Signal run time @ 20 °C	≤5.3 ns/m
Impedance @ 100 MHz	100 Ω ±5 %

## Material properties

Material (cable)	PVC
Colour (cable)	Green
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

Specifications	ISO/IEC 11801 EN 50173 IEC 24702 EN 50173-3 EN 50288-2-1 IEC 61156-5 IEC 60332-1-2 Flame retardancy UL 1581 UN/ECE-R 118 fire protection for rolling stock
UL / CSA	UL 444 DUZX.E333432 CSA-C22.2 No. 214 DUZX7.E333432
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	3,200 g



**Pushing Performance**  
Since 1945

## Commercial data

Net weight	66 g/m
Country of origin	Germany
European customs tariff number	85444995
GTIN	5713140061873
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249
UNSPSC 24.0	26121609