

RJ45 Han3A met. PN Cat5 PUR 5.0m




Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|-------------------------------------------------------------------------------|
| Part number | 09 45 700 0027 |
| Specification | RJ45 Han3A met. PN Cat5 PUR 5.0m |
| HARTING eCatalogue | https://harting.com/09457000027 |

Identification

| | |
|---------------|-----------------------------|
| Category | System cabling |
| Series | RJ45 |
| Element | Cable assemblies |
| Specification | Pre-assembled on both sides |
| Connector 1 | RJ45 |
| Connector 2 | Han® 3 A Metal |
| Type of cable | Copper cable (round) |

Version

| | |
|-----------------|-------------|
| Cable length | 5 m |
| Number of cores | 4 |
| Core structure | 4x AWG 22/7 |

Technical characteristics

| | |
|------------------------------|------------------------------|
| Transmission characteristics | Cat. 5 Class D up to 100 MHz |
| Data rate | 10 Mbit/s 100 Mbit/s |
| Limiting temperature | -40 ... +70 °C |

Material properties

| | |
|------------------|--------------------|
| Material (cable) | PUR (polyurethane) |
| Colour (cable) | Green |
| RoHS | compliant |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Specifications and approvals

| | |
|----------|-----|
| PROFINET | Yes |
|----------|-----|

Commercial data

| | |
|--------------------------------|----------------------------------------------|
| Packaging size | 1 |
| Net weight | 150.553 g |
| Country of origin | Romania |
| European customs tariff number | 85444290 |
| GTIN | 5713140267831 |
| eCl@ss | 27060390 Ready-made data cable (unspecified) |
| ETIM | EC002599 |
| UNSPSC 24.0 | 26121600 |