

RJ45 Han3A pla.Hyb. Cat6A+4x1,5 3.0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 725 1505
Specification	RJ45 Han3A pla.Hyb. Cat6A+4x1,5 3.0m
HARTING eCatalogue	https://harting.com/09457251505

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	Han [®] 3 A Hybrid Thermoplastic
Connector 2	Han [®] 3 A Hybrid Thermoplastic
Type of cable	Copper cable (round)

Version

Cable length	3 m
Number of cores	12
Core structure	4x 2x AWG 26/7 4x 1.5 mm ²

Technical characteristics

Transmission characteristics	Cat. 6 Class E up to 250 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s
Limiting temperature	-10 ... +70 °C



Pushing Performance
Since 1945

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	566.5 g
Country of origin	Romania
European customs tariff number	85447000
GTIN	5713140063174
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600