

RJ45 Han3A M.Hyb. Cat6A+4x1,5 2.0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 725 1534
Specification	RJ45 Han3A M.Hyb. Cat6A+4x1,5 2.0m
HARTING eCatalogue	https://harting.com/09457251534

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	Han [®] 3 A Hybrid Metal
Connector 2	Han [®] 3 A Hybrid Metal
Type of cable	Copper cable (round)

Version

Cable length	2 m
Number of cores	12
Core structure	4x 2x AWG 26/7 4x 1.5 mm ²

Technical characteristics

Transmission characteristics	Cat. 6 Class E up to 250 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s
Limiting temperature	-10 ... +70 °C



Pushing Performance
Since 1945

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	550.3 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140249943
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600