

## RJI coupler housing empty IP 65/67



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 805 0000
Specification	RJI coupler housing empty IP 65/67
HARTING eCatalogue	<a href="https://harting.com/09458050000">https://harting.com/09458050000</a>

### Identification

Category	Connectors
Series	HARTING RJ Industrial® RJ45
Element	Coupler

### Version

Details	Please order insert separately.
Pack contents	Hoods / Housings Seal membrane for 6 - 9 mm / 4.5 - 7.5 mm cable

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 / IP67
Cable diameter	6 ... 9 mm 4.5 ... 7.5 mm

### Material properties

Material (hood/housing)	Polyamide (PA)
Material flammability class acc. to UL 94	V-2
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances Not contained

California Proposition 65 substances Not contained

## Commercial data

Packaging size	1
Net weight	40 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140224599
eCl@ss	27440190 Industry connector (unspecified)
ETIM	EC001264
UNSPSC 24.0	39121409