

HPP V4 Power crimp cont. female 2,5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 46 500 0406
Specification	HPP V4 Power crimp cont. female 2,5mm ²
HARTING eCatalogue	https://harting.com/09465000406

Identification

Category	Contacts
Series	HARTING PushPull (V4)
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	2.5 mm ²
Conductor cross-section [AWG]	AWG 12
Mating cycles	≥750

Material properties

Material (contacts)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

Material properties

REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	100
Net weight	0.3 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140065499
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522