

## RJ45-RJ45,2x270°,90°ang.,AWG22/7; 0,5m



Image is for illustration purposes only. Please refer to product description.

Part number	09 47 030 3023
Specification	RJ45-RJ45,2x270°,90°ang.,AWG22/7; 0,5m
HARTING eCatalogue	<a href="https://harting.com/09470303023">https://harting.com/09470303023</a>

### Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING RJ Industrial®
Connector 2	HARTING RJ Industrial®
Type of cable	Copper cable (round)
Description of the cable	Angled top

### Version

Cable length	0.5 m
Number of cores	4
Core structure	4x AWG 22/7

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +70 °C

### Material properties

Material (cable)	PVC
Colour (cable)	Green



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Commercial data

Packaging size	1
Net weight	78.767 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140252172
eCl@ss	27060308 Patch cord copper (data cable)
UNSPSC 24.0	26121609