

RJI-RJ45,2x270°,90°ang.,AWG22/7; 10,0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 47 030 3034
Specification	RJI-RJ45,2x270°,90°ang.,AWG22/7; 10,0m
HARTING eCatalogue	https://harting.com/09470303034

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING RJ Industrial®
Connector 2	HARTING RJ Industrial®
Type of cable	Copper cable (round)
Description of the cable	Angled top

Version

Cable length	10 m
Number of cores	4
Core structure	4x AWG 22/7

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +70 °C

Material properties

Material (cable)	PVC
Colour (cable)	Green



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140065710
eCl@ss	27060308 Patch cord copper (data cable)
UNSPSC 24.0	26121609