

## RJ45 IP20/ 90° gew.2X180° 22/7;1,5m;flex.



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 47 050 5025                                                                |
| Specification      | RJ45 IP20/ 90° gew.2X180°<br>22/7;1,5m;flex.                                  |
| HARTING eCatalogue | <a href="https://harting.com/09470505025">https://harting.com/09470505025</a> |

### Identification

|                          |                             |
|--------------------------|-----------------------------|
| Category                 | System cabling              |
| Series                   | RJ45                        |
| Element                  | Cable assemblies            |
| Specification            | Pre-assembled on both sides |
| Connector 1              | HARTING RJ Industrial®      |
| Connector 2              | HARTING RJ Industrial®      |
| Type of cable            | Copper cable (round)        |
| Description of the cable | Angled left                 |

### Version

|                 |             |
|-----------------|-------------|
| Cable length    | 1.5 m       |
| Number of cores | 4           |
| Core structure  | 4x AWG 22/7 |

### Technical characteristics

|                              |                              |
|------------------------------|------------------------------|
| Transmission characteristics | Cat. 5 Class D up to 100 MHz |
| Data rate                    | 10 Mbit/s<br>100 Mbit/s      |
| Limiting temperature         | -40 ... +70 °C               |

### Material properties

|                  |       |
|------------------|-------|
| Material (cable) | PVC   |
| Colour (cable)   | Green |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| RoHS                                 | compliant     |
| ELV status                           | compliant     |
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Yes           |
| California Proposition 65 substances | Nickel        |

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 1                                       |
| Net weight                     | 160 g                                   |
| Country of origin              | Romania                                 |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140065888                           |
| eCl@ss                         | 27060308 Patch cord copper (data cable) |
| UNSPSC 24.0                    | 26121609                                |