

RJI M12Cord 4xAWG22/7outd 2xM12 - 2m



Image is for illustration purposes only. Please refer to product description.

Part number	09 47 222 2004
Specification	RJI M12Cord 4xAWG22/7outd 2xM12 - 2m
HARTING eCatalogue	https://harting.com/09472222004

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight
Connector 2	M12 D-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	2 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material (cable)	PVC
Colour (cable)	Black



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	173 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140247369
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600