

## RJ45 M12Cord 4xAWG22/7outd 2xM12 10m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 47 222 2011                                                                |
| Specification      | RJ45 M12Cord 4xAWG22/7outd 2xM12 10m                                          |
| HARTING eCatalogue | <a href="https://harting.com/09472222011">https://harting.com/09472222011</a> |

### Identification

|               |                               |
|---------------|-------------------------------|
| Category      | System cabling                |
| Series        | Circular connectors M12       |
| Element       | Cable assemblies              |
| Specification | Pre-assembled on both sides   |
| Connector 1   | M12 D-coding<br>Male Straight |
| Connector 2   | M12 D-coding<br>Male Straight |
| Type of cable | Copper cable (round)          |

### Version

|                 |             |
|-----------------|-------------|
| Cable length    | 10 m        |
| Number of cores | 4           |
| Core structure  | 4x AWG 22/7 |
| Coding          | D-coding    |

### Technical characteristics

|                              |                              |
|------------------------------|------------------------------|
| Transmission characteristics | Cat. 5 Class D up to 100 MHz |
| Data rate                    | 10 Mbit/s<br>100 Mbit/s      |

### Material properties

|                  |       |
|------------------|-------|
| Material (cable) | PVC   |
| Colour (cable)   | Black |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| ECHA SCIP number                     | 567c8b78-5fa0-43aa-a4c0-beb9d99b7769                   |
| California Proposition 65 substances | Yes                                                    |
| California Proposition 65 substances | Lead<br>Nickel                                         |

## Commercial data

|                                |                                              |
|--------------------------------|----------------------------------------------|
| Packaging size                 | 1                                            |
| Net weight                     | 695 g                                        |
| Country of origin              | Germany                                      |
| European customs tariff number | 85444290                                     |
| GTIN                           | 5713140247390                                |
| eCl@ss                         | 27060390 Ready-made data cable (unspecified) |
| ETIM                           | EC002599                                     |
| UNSPSC 24.0                    | 26121600                                     |