

M12 cord 4xAWG22/7 outd 2xM12 angl. 1.5m



Image is for illustration purposes only. Please refer to product description.

Part number	09 47 808 0003
Specification	M12 cord 4xAWG22/7 outd 2xM12 angl. 1.5m
HARTING eCatalogue	https://harting.com/09478080003

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Angled
Connector 2	M12 D-coding Male Angled
Type of cable	Copper cable (round)

Version

Cable length	1.5 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material (cable)	PVC
Colour (cable)	Black



Pushing Performance
Since 1945

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	10
Net weight	142.4 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140248052
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600