

M12 cord 4xAWG22/7 outd 2xM12 angl. 5m



Image is for illustration purposes only. Please refer to product description.

Part number	09 47 808 0006
Specification	M12 cord 4xAWG22/7 outd 2xM12 angl. 5m
HARTING eCatalogue	https://harting.com/09478080006

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Angled
Connector 2	M12 D-coding Male Angled
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material (cable)	PVC
Colour (cable)	Black



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
Net weight	382 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140248069
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600