

RJ45 PROFINET cable PVC 4p; Cat. 5; 15m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 686 8001 150
Specification	RJ45 PROFINET cable PVC 4p; Cat. 5; 15m
HARTING eCatalogue	https://harting.com/09486868001150

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING DualBoot RJ45
Connector 2	HARTING DualBoot RJ45
Type of cable	Copper cable (round)
Description of the cable	Straight

Version

Cable length	15 m
Number of cores	4
Core structure	4x AWG 22/7

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-25 ... +60 °C

Material properties

Material (cable)	PVC
Colour (cable)	Green



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
UL / CSA	UL 1863 DUXR.E470046 Raw cable UL rating 600 V
PROFINET	Yes

Commercial data

Packaging size	2
Net weight	1,001 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140067509
eCl@ss	27060308 Patch cord copper (data cable)
UNSPSC 24.0	26121609