

M12 PP X-coded RJ45 cable assy Cat6a,3m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 822 3757 030
Specification	M12 PP X-coded RJ45 cable assy Cat6a,3m
HARTING eCatalogue	https://harting.com/09488223757030

Identification

Category	System cabling
Series	Circular connectors M12 RJ45
Identification	PushPull
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 X-coding Male Straight PushPull
Connector 2	HARTING RJ Industrial® Gigalink Straight
Type of cable	Copper cable (round)

Version

Cable length	3 m
Number of cores	8
Core structure	4x 2 Twisted Pair
Coding	X-coding

Technical characteristics

Transmission characteristics	Cat. 6A Class EA up to 500 MHz
------------------------------	--------------------------------



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +70 °C

Material properties

Material (cable)	PVC
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140266711
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600