



Pushing Performance
Since 1945

VB RJ45 UaD -VB RJ45 UaD Cat.6A PUR 3.0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 848 4745 030
Specification	VB RJ45 UaD -VB RJ45 UaD Cat.6A PUR 3.0m
HARTING eCatalogue	https://harting.com/09488484745030

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING VarioBoot RJ45 Preferred directions up/down
Connector 2	HARTING VarioBoot RJ45 Preferred directions up/down
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Halogen-free Oil resistant

Version

Cable length	3 m
Number of cores	8
Core structure	4x 2x AWG 26/7

Technical characteristics

Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-30 ... +75 °C unmoved -5 ... +50 °C moved
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV 329)
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	ISO/IEC 11801 IEC 61156-6
UL / CSA	UL 1863 DUXR.E470046

Commercial data

Packaging size	1
Net weight	135 g
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140162235
eCl@ss	27060308 Patch cord copper (data cable)
UNSPSC 24.0	26121609