



Pushing Performance
Since 1945

VB RJ45 LaR -VB RJ45 LaR FRNC grey 1.0m




Image is for illustration purposes only. Please refer to product description.

Part number	09 48 858 5585 010
Specification	VB RJ45 LaR -VB RJ45 LaR FRNC grey 1.0m
HARTING eCatalogue	https://harting.com/09488585585010

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING VarioBoot RJ45 Preferred directions left/right
Connector 2	HARTING VarioBoot RJ45 Preferred directions left/right
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Flame retardant Halogen-free

Version

Cable length	1 m
Number of cores	8
Core structure	4x 2x AWG 26/7

Technical characteristics

Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-20 ... +60 °C unmoved
	0 ... +60 °C moved
Degree of protection acc. to IEC 60529	IP20
Minimum bending radius	10x Cable diameter (singular bending)
	5x Cable diameter (repeated bending)

Material properties

Material (cable)	FRNC (LSZH)
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV 329)
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	ISO/IEC 11801
	IEC 61156-6
	IEC 60332-1 Flame retardancy
	IEC 60754-2 Halogen freeness
	IEC 60754-2 Non corrosive
	IEC 61034 Low smoke

Commercial data

Packaging size	1
Net weight	11.852 g
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140250253
eCl@ss	27060308 Patch cord copper (data cable)
UNSPSC 24.0	26121609