



Pushing Performance
Since 1945

RJ45 Eco-I 90°-D F/UTP Cat.5e LSZH 10m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 E2E 27A7 100
Specification	RJ45 Eco-I 90°-D F/UTP Cat.5e LSZH 10m
HARTING eCatalogue	https://harting.com/0948E2E27A7100

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	RJ45 ECO-I Angled
Connector 2	RJ45 ECO-I Angled
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1

Version

Cable length	10 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Shielding	Shielded
Number of contacts	8
Locking type	Locking hook

Technical characteristics

Transmission characteristics	Cat. 5e Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
Limiting temperature	-20 ... +60 °C unmoved
	-20 ... +60 °C moved



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529 IP20 mated condition

Cable diameter	5.4 mm
----------------	--------

Material properties

Material (cable)	Halogen free polymer TM7 (LSZH)
------------------	---------------------------------

Colour (cable)	Grey
----------------	------

RoHS	compliant
------	-----------

ELV status	compliant
------------	-----------

China RoHS	e
------------	---

REACH Annex XVII substances	Not contained
-----------------------------	---------------

REACH ANNEX XIV substances	Not contained
----------------------------	---------------

REACH SVHC substances	Not contained
-----------------------	---------------

California Proposition 65 substances	Not contained
--------------------------------------	---------------

Specifications and approvals

Specifications	IEC 60603-7
	IEC 60332-1

Commercial data

Packaging size	1
----------------	---

Country of origin	Latvia
-------------------	--------

European customs tariff number	85444290
--------------------------------	----------

eCl@ss	27060308 Patch cord copper (data cable)
--------	---