

MPP-PFT-T1-F-P



Image is for illustration purposes only. Please refer to product description.

Part number	09 51 522 0001
Specification	MPP-PFT-T1-F-P
HARTING eCatalogue	https://harting.com/09515220001

Identification

Category	Connectors
Series	HARTING Mini PushPull
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Without board locks

Version

Locking type	PushPull
Details	Please order insert separately.
Pack contents	With adapter

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 / IP67

Material properties

Material (hood/housing)	Polybutylene terephthalate (PBT)
Colour (hood/housing)	Black
Material (seal)	PTS
Colour (seal)	Yellow
Material (adapter)	Polyamide (PA)
Colour (adapter)	Black
Material flammability class acc. to UL 94	V-0

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 63171-6
----------------	-------------

Commercial data

Packaging size	1
Net weight	4.5 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140570658
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466