

## MPP-ACC-DUST CAP PLUG IP65/67



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Accessories
Series	HARTING Mini PushPull
Type of accessory	Protection cover
Description of the accessory	for cable side

### Version

Locking type	PushPull
--------------	----------

### Technical characteristics

Limiting temperature	-40 ... +70 °C
Storage temperature	-60 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67

### Material properties

Material (accessories)	Polybutylene terephthalate (PBT)
Colour (accessories)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
----------	--

## Commercial data

Packaging size	1
Net weight	6.4 g
Country of origin	Romania
European customs tariff number	39269097
GTIN	5713140235588
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400