



Pushing Performance
Since 1945

37p ANG STD M PL3_M3 SL_Reel_140 pcs



Image is for illustration purposes only. Please refer to product description.

Part number	09 55 466 7821 741
Specification	37p ANG STD M PL3_M3 SL_Reel_140 pcs
HARTING eCatalogue	https://harting.com/09554667821741

Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector
Description of the contact	Stamped Angled

Version

Termination method	Reflow soldering termination (SMT)
Gender	Male
Size	D-Sub 4
Connection type	Motherboard to daughtercard
Number of contacts	37
Locking type	Fixing flange with fitted screw lock M3
Pack contents	140 pieces on reel

Technical characteristics

Contact spacing (termination side)	2.76 mm
Rated current	5 A
Clearance distance	≥1 mm
Creepage distance	≥1 mm
Insulation resistance	> 5 x 10 ⁹ Ω
Contact resistance	≤25 mΩ



Pushing Performance
Since 1945

Technical characteristics

Tightening torque	≤0.4 Nm Locking screw
Limiting temperature	-55 ... +125 °C (during reflow soldering max. +240 °C for 30 s)
Insertion force	≤123 N
Withdrawal force	≥11 N ≤82 N
Performance level	3
Mating cycles	≥50
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ($175 \leq CTI < 400$)
PCB thickness	≥1.6 mm
Installation height	7.3 mm
Hot plugging	No
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D
Process Sensitivity Level (PSL)	R0 acc. to ECA/IPC/JEDEC J-STD-020D

Material properties

Material (insert)	Liquid crystal polymer (LCP) Shell: steel, nickel plated
Colour (insert)	Black
Material (contacts)	Copper alloy Ground: Zinc die-cast
Surface (contacts)	Noble metal over Ni
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	DIN 41652
----------------	-----------



Pushing Performance
Since 1945

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	1
Net weight	23 g
Country of origin	Vietnam
European customs tariff number	85366990
GTIN	5713140219106
ETIM	EC001136
eCl@ss	27440214 D-Sub coupler