

PP SFP XS Recept.long, LC Dupl+col.-Clip



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 411 0501 201
Specification	PP SFP XS Recept.long, LC Dupl+col.-Clip
HARTING eCatalogue	https://harting.com/09574110501201

Identification

Category	Connectors
Series	PushPull XS SFP
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Long version for LC and RJ45 transceiver

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥50
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

Commercial data

Packaging size	50
Net weight	5 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140224087
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466