

Set Han3A M receptacle 2x LC dup. SM GOF



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	LC duplex
Series of hoods/housings	Han A®
Element	Panel feed through
Type of contact	LC contact
Description of the contact	Singlemode

Version

Size	3 A
Number of contacts	4

Technical characteristics

Limiting temperature	-40 ... +70 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	50.8 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140224148
eCl@ss	27440113 Rectangular connectors (set)
ETIM	EC002636
UNSPSC 24.0	39121408