

pdt Han3A AC LC duplex receptacle MM GOF



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 568 0500 000
Specification	pdt Han3A AC LC duplex receptacle MM GOF
HARTING eCatalogue	https://harting.com/09575680500000

Identification

Category	Connectors
Series	LC duplex
Identification	Hybrid
Series of hoods/housings	Han A [®]
Element	Panel feed through
Type of contact	LC contact
Description of the contact	Multimode
Type of hood/housing	Hood

Version

Size	3 A
Number of contacts	5
Number of power contacts	3
Number of special contacts	2x FO contact
Contact configuration	L1, PE, N

Technical characteristics

Rated voltage (power)	300 V AC
Limiting temperature	-40 ... +70 °C
Degree of protection acc. to IEC 60529	IP65 IP67



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	89.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140072794
eCl@ss	27440113 Rectangular connectors (set)
ETIM	EC002636
UNSPSC 24.0	39121408