

## UIC558-FC-CRT-0.75 mm<sup>2</sup>/ 18 AWG-NI



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 000 6605
Specification	UIC558-FC-CRT-0.75 mm <sup>2</sup> / 18 AWG-NI
HARTING eCatalogue	<a href="https://harting.com/09580006605">https://harting.com/09580006605</a>

### Identification

Category	Contacts
Series	HARTING UIC
Identification	UIC 558
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.75 ... 1 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 18
Rated current	≤10 A
Contact resistance	≤4 mΩ
Stripping length	7.5 mm
Mating cycles	≥10,000

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Nickel plated
RoHS	compliant
ELV status	compliant

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	-------------------------------------------------------------

## Commercial data

Packaging size	50
Net weight	2.2 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140188709
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522