

## UICIT\_WMRF 8



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods / Housings
Series	HARTING UIC
Identification	UIC IT
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With metal cover

### Version

Number of contacts	8
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Limiting temperature	-50 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 6005 (moos green)
Material (seal)	Silicone
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

## Commercial data

Packaging size	1
Net weight	0.61 kg
Country of origin	India
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466