

UICIT_WMRF 8/16



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 001 0313
Specification	UICIT_WMRF 8/16
HARTING eCatalogue	https://harting.com/09580010313

Identification

Category	Hoods / Housings
Series	HARTING UIC
Identification	UIC IT
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With metal cover

Version

Number of contacts	24
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-50 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 1003 (signal yellow)
Material (seal)	Silicone
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	1
Net weight	0.61 kg
Country of origin	India
European customs tariff number	85389099
GTIN	5713140492158
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466