

UIC558-HTE-22PIN-PG21



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 001 1442
Specification	UIC558-HTE-22PIN-PG21
HARTING eCatalogue	https://harting.com/09580011442

Identification

Category	Hoods / Housings
Series	HARTING UIC
Identification	UIC 558
Type of hood/housing	Hood

Version

Number of contacts	22
Version	Top entry
Number of cable entries	1
Cable entry	1x Pg 21
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-50 ... +125 °C
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	Black
Material (seal)	Silicone
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	180 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140183940
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466