

UIC558-13PIN-MI-CRT



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Series	HARTING UIC
Identification	UIC 558

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	13
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section [AWG]	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	60 V
Insulation resistance	>10 ⁷ Ω
Limiting temperature	-50 ... +125 °C
Mating cycles	≥10,000

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UIC 550 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	1
Net weight	37.045 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140186965
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522