

UIC558 18PIN-FI-CRT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 018 3101
Specification	UIC558 18PIN-FI-CRT
HARTING eCatalogue	https://harting.com/09580183101

Identification

Category	Inserts
Series	HARTING UIC
Identification	UIC 558

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	18
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section [AWG]	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	60 V
Insulation resistance	>10 ⁷ Ω
Limiting temperature	-50 ... +125 °C
Mating cycles	≥10,000

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black

Material properties

Material flammability class acc. to UL 94	V-0
---	-----

Specifications and approvals

Specifications	UIC 550 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	1
Net weight	87 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140186996
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522