

UICIT_WMRF 8/16_DUMMY KIT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 024 1033
Specification	UICIT_WMRF 8/16_DUMMY KIT
HARTING eCatalogue	https://harting.com/09580241033

Identification

Category	Connector sets
Series	HARTING UIC
Identification	UIC IT
Element	Connector sets
Specification	Dummy kit

Version

Gender	Female
--------	--------

Technical characteristics

Conductor cross-section	1 mm ² Signal
Conductor cross-section [AWG]	Data
	AWG 18 Signal
Insulation resistance	>10 ⁷ Ω
Tightening torque	5 Nm Fixing screws M6
Limiting temperature	-40 ... +90 °C
Mating cycles	≥10,000
Degree of protection acc. to IEC 60529	IP67 / IP69

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (hood/housing)	Aluminium die-cast
	Corrosion resistant



Pushing Performance
Since 1945

Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 1003 (signal yellow)
Material (seal)	Silicone
Material (locking)	Stainless steel
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	0.661 kg
Country of origin	India
European customs tariff number	85366990
GTIN	5713140492172
eCl@ss	27440115 Circular connector (set)
ETIM	EC002635
UNSPSC 24.0	39121413