

Han 3EMC-HBM-SL (only f. PCB-adapter)



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® EMC
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight for PCB termination with Han® Q 5/0

Version

Size	3 A
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

Technical characteristics

Tightening torque	1 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated

Material properties

Colour (hood/housing)	Unpainted
Material (seal)	PTFE
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	10
Net weight	32.56 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140073012
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466