

## Han EMC/B 6 Protect Cover metal



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 62 806 5425                                                                |
| Specification      | Han EMC/B 6 Protect Cover metal                                               |
| HARTING eCatalogue | <a href="https://harting.com/09628065425">https://harting.com/09628065425</a> |

### Identification

|                              |                                                                                   |
|------------------------------|-----------------------------------------------------------------------------------|
| Category                     | Accessories                                                                       |
| Series of hoods/housings     | Han <sup>®</sup> EMC/B                                                            |
| Type of accessory            | Protection cover                                                                  |
| Description of the accessory | for bulkhead mounted housings<br>for surface mounted housings<br>With fixing cord |

### Version

|              |                                                |
|--------------|------------------------------------------------|
| Size         | 6 B                                            |
| Locking type | Single locking lever                           |
| Details      | Not suitable for housings with external seals. |

### Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |
| Type rating acc. to UL 50 / UL 50E     | 4<br>12         |

### Material properties

|                         |                    |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing)  | Uncoated           |
| Colour (hood/housing)   | Unpainted          |
| RoHS                    | compliant          |
| ELV status              | compliant          |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Yes           |
| California Proposition 65 substances | Lead          |
|                                      | Nickel        |

## Specifications and approvals

|           |                                   |
|-----------|-----------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076             |
|           | CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | DNV GL                            |

## Commercial data

|                                |                                        |
|--------------------------------|----------------------------------------|
| Packaging size                 | 1                                      |
| Net weight                     | 44 g                                   |
| Country of origin              | Germany                                |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140191891                          |
| eCl@ss                         | 27440208 Cap for industrial connectors |
| ETIM                           | EC002314                               |
| UNSPSC 24.0                    | 39121467                               |