

D-Sub, FE AWG 22-26 crimp cont



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 000 5476
Specification	D-Sub, FE AWG 22-26 crimp cont
HARTING eCatalogue	https://harting.com/09670005476

Identification

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section (mm ²)	0.13 ... 0.33 mm ²
Conductor cross-section (AWG)	AWG 26 ... AWG 22
Contact resistance	≤10 mΩ
Stripping length	4.5 mm
Performance level	1 acc. to CECC 75301-802

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight



Pushing Performance
Since 1945

Material properties

ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	100
Net weight	0.226 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140086593
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522